




The inlets and outlets are located on the base, while the drive shaft may protrude from the same side or opposite side. This range of pumps is designed for applications requiring compact overall dimensions. The fixing of the pump to the distributor or the electric motor is via the same screws of the pump, once unscrewed and deleted the No. 4 M4 nuts.


**Options:**

- A = N. 2 through holes  $\varnothing = 4.1$  mm, distance 48 mm.

**POM-GRAZ27**



i



\* Displacement: 0,52 cc.



# Standard Compact Pump Typical curves

